



Giotto FullControl

Advanced tube-tube-sheet TIG orbital welding system

Welding

TIG Orbital welding







A winning story since 1961

The Beginning

At the end of the 1950s, Domenico Franco Agostino became the Italian representative of Albert Otto, a German manufacturer of tube expanders. In 1961 Franco Agostino's Albert Otto Italiana was founded and in 1972, after purchasing an area of 10,000 square metres in the municipality of Bagnolo Cremasco, Maus Italia Sas was established.

The Growth

In 1976 his son Stefano, a mechanical engineer, joined the company. Together with his father, he studied products, introduced new machinery onto the market and filed the first patents by Maus Italia. Above all, Stefano was firmly convinced that people are the very heart of a company's success. Therefore, he invested in human capital by valuing people and roles, and he surrounded himself with skilled operators as well as technical, commercial and administrative collaborators. The result was a winning, competent and proactive team.

His daughter Anna - also a mechanical engineer - has been working in the company since 2016, giving new impetus and energy to the business her father and grandfather had built.

Father and daughter work together side by side every day to guarantee the excellence of Maus Italia and support all customers worldwide with competence and passion: the company's distinctive traits.



Stefano Agostino CEO - Mechanical Engineer

Anna Agostino

COO - Mechanical and Management Engineer











In-house production of each component Workshop 4.0 and 24/7 production control

The production of Maus Italia branded items is entirely carried out in Bagnolo Cremasco, in the heart of an Italian industrial area 30 km southeast of Milan.

The company boasts a 4.0 workshop equipped with state-of-the-art machinery, an in-house heat treatment room and a final inspection department that allow Maus Italia to independently manage every phase of the manufacturing process of its wide range of products whilst maintaining high quality standards.



Quality first. Design and development

One of Maus Italia's strengths is its willingness to understand its customers' needs.

Our technical department is always ready to find operational solutions to the most complex applications, even via feasibility studies. We develop accurate work processes, draw with FEM analyses to verify our mechanical-structural performance and optimise the manufacturing process of each component.

Ready To Deliver

A well-stocked and complete warehouse of finished products enables Maus Italia ship quickly to customers all over the world according to a ready-to-deliver logic.

The warehouse is fully located within our premises in Bagnolo Cremasco at controlled temperatures and conditions to guarantee the maximum safety and quality of Maus Italia products for all our customers.

Quality, environment and safety policy

Research, quality and safety are the watchwords of Maus Italia Spa.

Maus Italia has several projects underway aimed at increasingly sustainable development and integrates environmental concerns into its business model. The company's actions, behaviour and development choices are focused not only on the short run but rather mainly on a medium and long-term horizon.



Every day in over 80 country worldwide

Find an official distributor in your country





Pag. 3 ENG / REV 01/23





Giotto FullControl

Advanced system for a total control of tube-tube-sheet TIG orbital welding

Maus Italia presents the *Giotto FullControl system*, top-of-the-range trolley-mounted semi-automatic systems for heat exchanger tube-tube-sheet orbital welding. In-house design and construction has allowed this product to be optimised, providing a high quality system, composed by:

- A Giotto FC 250 orbital head for tube-tubesheet TIG welding
- Giotto PG 300 programmer/generator with microprocessor inverter complete with cooling unit and touchscreen interface
- Accessories, options and spare parts to meet every need for welding tubes to the tube-sheet

Extremely precise

Revolutionary features

Fixed angle - Electrode incidence setting

Adjustable wire feed unit

Single key adjustments

Continuous recording of the weld

Remote control with display

Protective gas line



Pag. 6 ENG / REV 01/23

Focus features



Electrode angle setup

The electrode holder system with preset angles adapts to any welding geometry and makes setup easy and repeatable.



Sectors

The division into up to 9 sectors of the welding cycle allows compensation for the negative effects of gravity on the welding puddle.



Adjustments with a single key

All available adjustments for different welding geometries require a single supplied key.



24/7 Usage

The enhanced cooling system inside the head allows intensive use of the system.



Continuous recording of the weld

All work parameters can be stored on a USB pen drive and printed on board the machine.



Test gas

The operator has the option to check and adjust the flow of the gas to the flowmeter before the start of the welding cycle.



Remote control with display

Simple and intuitive interface for control of welding parameters. Comes complete with all manual controls for the welding head.



Protective gas line

There is an additional dedicated gas line, inside the body of Giotto FC 250, for the external protection of welding.

Optionals




IWFG Filler wire

Rotating supply unit for the filler wire.





Thrust devices

Mounted on the welding head, these allow welding of flush or protruding tubes and, when necessary, for welding in a protected atmosphere.



Pag. 7 ENG / REV 01/23






- a welding thickness
- OD external diameter of the pipe
- g gap between external tube diameter and tube sheet hole
- t tube thickness

- t1 thickness of plating
- t2 thickness of the tube-sheet
- x weld overflow

Pag. 8 ENG / REV 01/23





Advanced tube to tubesheet TIG orbital welding system

Advanced portable product, suitable for complex applications. Stands out for its reliability, precision, ease of use and robustness.

Reliable

Precise

Ergonomic

Standard supply

Giotto FC 250 Giotto PG 300

- Orbital head with cables (torch power/ cooling)
- Trolley-mounted digital programmer generator with inverter
- Remote control with display
- Ground wire
- Digital gauge
- Electrode holder bracket kit with various angles of incidence
- Welding head adjustment and maintenance kit
- Instruction manual
- Carrying case



Optionals

Argo clamp

TIG orbital welding head centring and locking system

IWFG

Rotating filler wire supply unit

WTC-FT


WTC-PT

Thrust device for welding flush tubes with BlockOut anti-glare screen

Four-point thrust device for welding protruding (or recessed) tubes


WTC-GAS2

Thrust device for welding tubes in a protected atmosphere




Test X-ray

Tube & 26,7 mm x 2,87 mm (1.051" x 0.113") ASTM A210 Material Tube overhang 5 mm (0.197") Tube-sheet thickness 30 mm (1.181")



Test X-ray

1.3/4" Tube - 10 BWG Material TP 316 L Tube overhang 5 mm (0.197") Tube sheet thickness 30 mm (1.181")



Micrometer adjustement

Device for adjusting the distance of the electrode from the tube-sheet.

Complete range of devices for centring in the tube consisting of HS cartridge spindles and HC self-centring cartridges.

Different WTC thrust devices to be selected on the based of tube geometry and material, with Maus Italia BlockOut screens for anti-dazzle protection.





Single key Adjustable filler wire feed unit

All adjustments are made with a single supplied key.



New electrode tightening system

MALS Giotto FC 250


The tangential screw does not require service keys and speeds up replacement of the worn electrode without touching other parts that could change the geometric setting.

Pag. 11 ENG / REV 01/23



Tube-tube-sheet TIG orbital welding head


The Giotto FC 250 head is the result of extensive development and prototyping. Each component is designed and manufactured by Maus Italia.






Electrode angle setup guaranteed

Thanks to components with predetermined angles, the proposed system for each welding geometry is absolute and repeatable. It facilitates geometric setup operations as well as being extremely stable and robust.



Pag. 12 ENG / REV 01/23







Speed adjustement

Programming of the peripheral speed of head rotation.



Precise position

Absolute optical control of the angular position using an encoder.



Protective gas line

There is an additional gas line, inside the body of the Giotto **FC 250**, dedicated to the external protection of the weld for combination with the **WTC-Gas2** thrust device.


HC Self-centring cartridge



Welding with the ideal temperature

The effective internal cooling system of the **Giotto FC 250** orbital welding head guarantees:

- control of the internal temperature of the rotating joint even at high welding amperages;
- continuous use in 24/7 shifts;
- high quality of the welding puddle with a lower average temperature of the electrode and the protective gas passing through it;
- significant improvement in welding performance.







Digital programmer/generato with inverter with integrated-control microprocessor and digital interface on monitor

Powerful and compact, Maus Italia's offers the Giotto PG 300 programmer/generator for controlling the TIG Giotto FC 250 orbital welding head to guarantee 100% repeatability. Mounted on "carriage pickUp" with gas bottle holder

Powerful

Compact

Ergonomic



Pag. 16 ENG / REV 01/23



Pre-weld gas control

The operator, using the remote control, has the possibility of checking and adjusting the flow of the gas to the flowmeter before the start of the welding cycle.



Welding sectors

There is the option to program, using the integrated software, subdivisions of up to 9 sectors of the welding cycle to compensate for the negative e ects of gravity on the welding puddle.




Operator panel on color monitors

This is the interface where the working parameters (and setting) of the orbital head are programmed and displayed.

Thanks to the integrated 12.1" monitor, backlit in colors (capacitive touch - screen), parameter programming is extremely fast and simple.





Available parameters

- Date and time
- Serial number of the generator
- Serial number of the connected gun
- Operator
- Name of welding program in use
- > Angular position of the torch
- Time in seconds from the beginning of the cycle.
- Average current value
- Average voltage value.
- Peripheral speed of the orbital head.
- > Speed of the filler wire.
- Applied energy.
- Pre-gas
- Starting current
- Slope times

- Welding puddle formation time
- Welding current
- Base current
- Pulse frequency
- Pulse balancing
- Final current
- Post gas time
- Welding speed
- Amount of filler wire
- Programmable sectors: 1 to 9 plus slopes
- Programmable up- and downslopes
- Program diagnosis simulation cycle
- Continuous recording of heat input (applied energy in kJ)

Dedicated TIG orbital welding programming and diagnostics software

The Giotto FullControl is supplied with dedicated Maus Italia software for intuitive programming of all welding parameters and prompt intervention of complete diagnostics for any malfunctions.

The simulation cycle allows you to try programs stored by the operators in advance (with space available for over 200 programs).

Optional

Maus Italia machines transform you into a Smart Factory!

Compliance of the Giotto FullControl system with the requirements of the "INDUSTRY 4.0" system, has been examined by an accredited Third party and considered suitable to allow interconnection between the machine and company systems.




Pag. 18 ENG / REV 01/23



Parameter monitor

Clear real-time display of the main welding parameters to allow the operator immediate feedback.



Welding sectors

- Definition of the number of sectors (1 to 9) and programming of parameters for each sector.
- > Control of the arc when shutting down




Continuous welding recording

All work parameters can be stored on a USB pen drive and printed on board the machine:


• in "time lapse" (for rotation angle/weld no.)





Welding head setup - Ignition

- Fundamental variables to guarantee total repeatability. Facilitate the exchange of correct information between operators.
- Definition of the welding start phase



Shut-down - Reports

- > Definition of the final welding phase
- > Enabling of welding report production modes



Remote control with display

Simple and intuitive interface for controlling the welding parameters. Complete with all manual welding head controls as well as:

- start-up
- stop
- · test gas
- on/o filler wire selector.

Supplied with 8 m (26 ft) connection cable



Optional components

IWFG filler wire feed unit and WTC thrust devices for the Giotto FC 250 tube-tube-sheet TIG orbital welding head



Rotating filler wire supply unit for wire from Ø 0.8 to 1 mm (0.0315" to 0.0394") in 1 kg coils (2.2 lb)

Guarantees regular supply of the wire to the welding puddle. Wire consumption is always in full view of the operator thanks to the transparent protective cloche.







With manual manoeuvring levers for quick adaptation to the tube pitch.





Multiple welders can operate simultaneously on the same tube-sheet to increase productivity.




The protective atmosphere is created by injection of inert gas into the thrust device with the aim of eliminating any contamination

Pag. 20 ENG / REV 01/23



WTC-PT

4-point of contact thrust device for welding protruding tubes








WTC-FT


Thrust device for welding flush or recessed tubes with rotating **BlockOut** anti-dazzle screen





WTC-Gas2

Thrust device for welding tubes in a protected atmosphere





Pag. 21 ENG / REV 01/23

Argo clamp

TIG orbital welding head centring and locking system

Argoclamp ensures centring and precise support of the head to the tube to be welded. Maus Italia, thanks to experience of its already patented products using radial caliper expanding tools, fits this technology directly on the Giotto FC 250 welding head. Argoclamp instantly expands inside the tube to be welded, locking the orbital head. The Argoclamp is powered by the protective gas dedicated to the torch electrode.











Disarmed Argo clamp for insertion and removal of the HP self-centering cartridge n the tube to be welded.



Active Argoclamp for centring and locking the head in the tube to be welded.






Pag. 22 ENG / REV 01/23

HP Centring for FC AG 250 welding head

Special centring to support the Argo clamp system (FC AG 250 welding head + PG 300 AG generator)

Special HP centring is interchangeable with the standard centering system consisting of HC cartridges and HS spindles.



	Tube	Cartridge	
		HP	
	mm	inches	Cod.
	12,0 ÷ 12,5	0.472 ÷ 0.492	HP-5
	12,5 ÷ 13,0	0.492 ÷ 0.512	HP-6
	12,8 ÷ 14,0	0.504 ÷ 0.551	HP-7
	13,3 ÷ 14,5	0.524 ÷ 0.571	HP-7A
ery	13,8 ÷ 15,0	0.543 ÷ 0.590	HP-8
eliv	14,3 ÷ 15,5	0.563 ÷ 0.610	HP-8A
ARI te d	14,8 ÷ 16,0	0.583 ÷ 0.630	HP-9
STANDARD for immediate delivery	15,8 ÷ 17,0	0.622 ÷ 0.669	HP-10
ST,	16,8 ÷ 18,0	0.661 ÷ 0.709	HP-11
or ir	17,8 ÷ 19,0	0.701 ÷ 0.748	HP-12
4	18,8 ÷ 20,5	0.740 ÷ 0.807	HP-13
	19,3 ÷ 21,5	0.760 ÷ 0.846	HP-13A
	19,8 ÷ 22,5	0.779 ÷ 0.886	HP-14
	20,9 ÷ 23,8	0.823 ÷ 0.937	HP-14A
	22,3 ÷ 25,0	0.878 ÷ 0.984	HP-15
	24,5 ÷ 27,0	0.965 ÷ 1.060	HP-16
	26,5 ÷ 29,0	1.043 ÷ 1.141	HP-17
	28,5 ÷ 31,2	1.122 ÷ 1.220	HP-18





The management system of Argo clamp pneumatic drive take place from the welding gas already present on board.



Argo clamp activation is ergonomically positioned on the welding head.

Pag. 23 ENG / REV 01/23







Sliding horizontal trolley-mounted deck for welding head support using balancer

With the aim of providing customers with every accessory necessary for tube-tube-sheet TIG orbital welding, Maus Italia has designed the Slide Deck sliding trolley-mounted deck, available in two sizes:

- > Giotto Slide Deck 1800
- Giotto Slide Deck 2800

Supplied in assembly kit, the Slide Deck allows the operator to connect the TPB-3A series balancer (supplied separately).

Improved stability

Less operator fatigue




Pag. 26 ENG / REV 01/23



Dimensions			1800	2800
Width	W	mm inches	2060 81.1	2860 112.6
Depth	D	mm inches	1390 54.7	1450 57.1
Height	Н	mm inches	2800 110.2	2900 114.2
Useful hight	Hu	mm inches	2400 94.5	2500 98.4
Capacity		kg Ib	50 110	45 99
Weight		kg Ib	150 330	170 374

Shipping						
Width	cm	ft	160	5.3	160	5.3
Depth	cm	ft	60	2.0	60	2.0
Height	cm		50	1.7	50	1.7
Crate weight	kg	lb	35	78	35	78
Total weight	kg	lb	185	408	185	408



Slider

The sliding system is designed to give stability and manoeuvrability to the horizontal movement of the welding head in front of the tube-sheet.

Each Giotto Slide Deck includes a Slider for connecting a TPB-3A balancer (supplied separately) for vertical movement of the welding head.

There is the option, on request, to install up to 3 Slider (2 optional) for the manoeuvring of 3 Giotto FC 250 welding heads.

TPB-3A

(Optional)

Spring balancer for the support and vertical movement of the welding head with a capacity of 10 to 14 kg (22.0 to 30.8 lb).



Pag. 27 ENG / REV 01/23



Balanced potential power supply for the simultaneous use of two welding systems

To promote increased productivity, Maus Italia suggests the simultaneous use of two or more Giotto FullControl systems with the relevant TIG GiottoFC250 orbital heads on the same tube-sheet.

Giotto Equipower 20 is equipped with a three-phase transformer and connection point to balance the power supply to the two connected welding systems.

Giotto Equipower 20 prevents welding systems from interfering each other during production with changes in the electrical network ensuring the right protection to the programmers' electronics.


Protection for electronics on board the machine

Avoid mains power supply disturbances




Pag. 28 ENG / REV 01/23





Power supply									
Supply voltag	V	olt - Ph	400/440/480 - 3						
OUT Voltage	V	olt - Ph		2x400 - 3					
Dimensions									
Width	W	mm	inches	600	23,6	•			
Depth	D	mm	inches	450	17.7				
Height	Н	mm	inches	615	24.2				
Weight		kg	lb	150	330				

Different INPUT voltage * available on request



Pag. 29 ENG / REV 01/23



Service trolley and storage for spare parts

A tidy and well-organised workspace is synonymous with e ciency and good practice.

The Giotto Service Trolley allows you to organise the consumable spare parts for Giotto orbital heads and to store all the keys and service accessories.

- > Three drawers mounted on telescopic ball rails with centralised front security lock.
- > Large thermoplastic work top
- > Orbital head support ensuring stability and functionality
- > Lower shelf with rubber mat
- > Equipped with 4 wheels of 0 125 mm

Rapid maintenance

Everything always in order and protected




Pag. 30 ENG / REV 01/23




Dimensions					
Width	W	mm	inches	740	29.1
Width + head	Wн	mm	inches	900	35.4
Depth	D	mm	inches	450	17.7
Height	Н	mm	inches	895	35.2
Height + head	Нн	mm	inches	1160	45.7
Capacity		kg	lb	400	881
Weight		kg	lb	41	90






Pag. 31 ENG / REV 01/23




Technical features

Technical features of the advanced tube-tube-sheet TIG orbital welding system


General features				
Duty Cycle			Α (60%)	250
Orbital welding speed (max)		rŗ	om	10
ID Tube (min.)		mm	inches	8 0.315
OD Tube standard (max.)		mm	inches	51 2.008
Welding head cooling				closed liquid circuit
Welding geometry				
Flush				~
Recessed (max.)		mm	inches	3,0 0.118
Protruding (max.)		mm	inches	12,0 0.472
Tungsten				
Ø 1.6				optional
∂ 2.4				standard
Ø 3.2				optional
Elastrada diatanas adiustman	+			manual
Electrode distance adjustmen	ι	mm	inches	12 (±6) 0.472(±0.236)
Filler wire				
Wire coil (weight/0)		kg/m	lbs/inches	1/100 2.21/3.937
wife con (weight/6)		Kg/III	150, 11101100	
Recommended wire diamete	r	mm	inches	0,8 0.0315
	r		·	0,8 0.0315 0,6 0.0236
Recommended wire diamete	r	mm	inches	
Recommended wire diameter • Wire diameter (optional)	r	mm mm	inches	0,6 0.0236
Recommended wire diameter • Wire diameter (optional) • Wire diameter (optional)		mm mm mm	inches inches	0,6 0.0236 1,0 0.0394
Recommended wire diamete · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional)		mm mm mm	inches inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5
Recommended wire diamete • Wire diameter (optional) • Wire diameter (optional) • Wire diameter (optional) Wire speed (max.)		mm mm mm mm	inches inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5
Recommended wire diamete · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions	m	mm mm mm mm	inches inches inches inches inches/min	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21
Recommended wire diamete · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height	W D H	mm mm mm mm	inches inches inches inches/min	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19
Recommended wire diamete · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring)	W D H	mm mm mm mm mm/min	inches inches inches inches inches/min inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21
Recommended wire diamete · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height	W D H	mm mm mm mm im/min mm mm	inches inches inches inches inches/min inches inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19
Recommended wire diameter • Wire diameter (optional) • Wire diameter (optional) • Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length	W D H	mm mm mm mm mm/min mm mm kg	inches inches inches inches/min inches inches inches inches inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5
Recommended wire diameter • Wire diameter (optional) • Wire diameter (optional) • Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length	W D H	mm mm mm mm mm/min mm mm kg	inches inches inches inches/min inches inches inches inches inches inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5 6 19.7
Recommended wire diameter · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length Packaging Width	W D H	mm mm mm mm mm/min mm mm kg	inches	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5 6 19.7
Recommended wire diameter · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length Packaging Width Depth	W D H	mm mm mm mm/min mm mm kg m	inches inches inches inches inches/min inches inches inches ft ft ft	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5 6 19.7
Recommended wire diameter · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length Packaging Width Depth Height	W D H	mm mm mm mm mm mm mm mm mm cm cm cm	inches in	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5 6 19.7 70 2.3 52 1.7 30 1.0
Recommended wire diameter · Wire diameter (optional) · Wire diameter (optional) · Wire diameter (optional) Wire speed (max.) Dimensions Width Depth (without centring) Height Weight excluding cables and Cable length Packaging Width Depth	W D H	mm mm mm mm mm mm mm kg m	inches inches inches inches inches/min inches inches inches ft ft ft	0,6 0.0236 1,0 0.0394 1,2 0.0472 2000 78.5 150 6 530 21 475 19 12 26.5 6 19.7





Pag. 33 ENG / REV 01/23









Power supply		
Supply voltage (±10%)	Volt - Ph	400 - 3
Absorbed power	kW	10
Network fuses	А	16
Cos fi / efficiency		0,99 / 84%
Open circuit voltage	Vdc	63
Utilisation factor (40°C/104°F X=60%)	А	250
(40°C/104°F X=100%)	А	210
Capacity		
Cooling power (25°C./77°F.)	W	650
Liquid coolant tank	I US gal	2,0 0.53
Coolant flow (max.)	I/min US gpm	3,3 0.87
Dimensions		
Width W	mm inches	670 26.4
Depth D	mm inches	1180 46.5
Height (transport)	mm inches	1210 47.7
Height (usage) Hu	mm inches	1510 59.5
Weight (without cylinder)	kg lb	125 276
Degree of protection	IP	23

Shipping (with Giotto FC 250 head case)		
Width	cm inches	80 2.7
Depth	cm inches	130 4.3
Height	cm inches	145 4.8
Crate weight	kg lb	8 18
Total weight	kg lb	152 334

Pressure reducer for 50-litre argon cylinders



Work cycle

250 A (40°C./104°F.) 60%

210 A (40°C./104°F) 100%

Pag. 35 ENG / REV 01/23







EXpandable sector cartridge mod. *HSE*

Self-centring system particularly suitable in tube-tube-sheet welding of boilers for internal diameters greater than 57 mm (2.1/4") and in vertical negative head applications (sugar refinery exchangers) where the support of the orbital welding head is guaranteed by the expansion of the sectors.





Pag. 36 ENG / REV 01/23

The centring of the torch is guaranteed by the spindle + cartridge system. Use the table to select the correct combination of the HS series spindle and the HC series cartridge according to the internal diameter of the tube.

Giotto FC 250

Centring

HS cartridge spindles and HC self-centering cartridges for Giotto FC AG 250 tube-tube-sheet TIG orbital welding head.


	Tube	size	Cartridge	Spindle	cartridges for Giotto FC AG 250 tube-tube-sheet TIG orbital welding head.
	TI II	D	HC	HS	Will state of the
	mm	inches	Cod.	Cod.	
	7,4 ÷ 7,8	0.291 ÷ 0.307	HC-76		
	7,7 ÷ 8,3	0.303 ÷ 0.327	HC-80		<u>_</u>
	8,2 ÷ 8,9	0.323 ÷ 0.350	HC-87	HS-MINI	
	8,5 ÷ 9,3	0.335 ÷ 0.366	HC-90		
	8,8 ÷ 9,7	0.346 ÷ 0.381	HC-95		
	9,8 ÷ 10,3	0.386 ÷ 0.466	HC-0		
	10,0 ÷ 10,5	0.394 ÷ 0.413	HC-1		
	10,5 ÷ 11,0	0.413 ÷ 0.433	HC-2		
	11,0 ÷ 11,5	0.433 ÷ 0.453	HC-3	HS-A	
	11,5 ÷ 12,0	0.453 ÷ 0.472	HC-4	113-A	
	12,0 ÷ 12,5	0.472 ÷ 0.492	HC-5		
	12,5 ÷ 13,0	0.492 ÷ 0.512	HC-6		
	12,8 ÷ 14,0	0.504 ÷ 0.551	HC-7		
	13,3 ÷ 14,5	0.524 ÷ 0.571	HC-7A		
	13,8 ÷ 15,0	0.543 ÷ 0.590	HC-8		
	14,3 ÷ 15,5	0.563 ÷ 0.610	HC-8A		
ery	14,8 ÷ 16,0	0.583 ÷ 0.630	HC-9		
eliv	15,8 ÷ 17,0	0.622 ÷ 0.669	HC-10		
te d	16,8 ÷ 18,0	0.661 ÷ 0.709	HC-11	HS-B	
dia	17,8 ÷ 19,0	0.701 ÷ 0.748	HC-12		
Jme	18,8 ÷ 20,5	0.740 ÷ 0.807	HC-13		
r in	19,3 ÷ 21,5	0.760 ÷ 0.846	HC-13A		
- fe	19,8 ÷ 22,5	0.779 ÷ 0.886	HC-14		
STANDARD - for immediate delivery	20,9 ÷ 23,8	0.823 ÷ 0.937	HA-14A		
ND/	22,3 ÷ 25,0	0.878 ÷ 0.984	HC-15		
STA	24,5 ÷ 27,0	0.965 ÷ 1.06	HC-16		
	26,5 ÷ 29,0	1.043 ÷ 1.141	HC-17		
	28,5 ÷ 31,	1.122 ÷ 1.220	HC-18		
	30,5 ÷ 33,0	1.201 ÷ 1.299	HC-19		
	32,5 ÷ 36,0	1.279 ÷ 1.417	HC-20	HS-C	
	35,5 ÷ 39,0	1.398 ÷ 1.535	HC-21		
	38,5 ÷ 42,0	1.516 ÷ 1.653	HC-22		
	41,5 ÷ 45,0	1.634 ÷ 1.772	HC-23		
	44,5 ÷ 48,0	1.752 ÷ 1.890	HC-24		
_	47,5 ÷ 51,0	1.870 ÷ 2.008	HC-25		
	50,5 ÷ 54,0	1.988 ÷ 2.126	HC-26		-
	53,5 ÷ 58,0	2.106 ÷ 2.283	HC-27		
	57,5 ÷ 62,0	2.264 ÷ 2.441	HC-28	HS-D	
	61,5 ÷ 68,0	2.421 ÷ 2.677	HC-29		
	65,5 ÷ 70,0	2.579 ÷ 2.756	HC-30		

Pag. 37 ENG / REV 01/23





BWG Table



Pag. 40 ENG / REV 01/23

1 2 BW		1 .		1 . BV		1 :		1 BV		1 BV		1 .		1 .		2 BV		2 BV		2 BV		23 BWG		24 BWG		OD "
" 0.109	mm 2,77	" 0.095	mm 2,41	<i>"</i> 0.083	mm 2,11	" 0.072	mm 1,83	<i>ιι</i> 0.065	mm 1,65	" 0.058	mm 1,47	<i>ιι</i> 0.049	mm 1,24	" 0.042	mm 1,07	" 0.035	mm 0,89	" 0.032	mm 0,81	" 0.028	mm 0,71	" 0.025	mm 0,64	" 0.022	mm 0,56	mm ← S p
-	-	-	-	-	-	-	-	-	-	-	-	0.152	3,8	0.166	4,1	0.180	4,5	0.186	4,7	0.194	4,9	0.200	5,0	0.206	5,2	1/4" (6,3)
-	-	-	-	0.209	5,3	0.231	5,8	0.245	6,2	0.259	6,5	0.277	7,0	0.291	7,3	0.305	7,7	0.311	7,9	0.319	8,1	0.325	8,2	0.331	8,4	3/8" (9,5)
-	-	0.310	7,9	0.334	8,5	0.356	9,0	0.370	9,4	0.384	9,7	0.402	10,2	0.416	10,5	0.430	10,9	0.436	11,1	0.444	11,3	0.450	11,4	0.456	11,6	1/2" (12,7)
0.407	10,3	0.435	11,1	0.459	11,7	0.481	12,2	0.495	12,6	0.509	12,9	0.527	13,4	0.541	13,7	0.555	14,1	0.561	14,3	0.569	14,5	0.575	14,6	0.581	14,8	5/8" (15,9)
0.532	13,4	0.560	14,2	0.584	14,8	0.606	15,3	0.620	15,7	0.634	16,0	0.652	16,5	0.666	16,8	0.680	17,2	0.686	17,4	0.694	17,6	0.700	17,7	0.706	17,9	<i>3/4"</i> (19,0)
0.657	16,6	0.685	17,4	0.709	18,0	0.731	18,5	0.745	18,9	0.759	19,2	0.777	19,7	0.791	20,0	0.805	20,4	0.811	20,6	0.819	20,8	0.825	20,9	0.831	21,1	7/8" (22,2)
0.782	19,8	0.810	20,6	0.834	21,2	0.856	21,7	0.870	22,1	0.884	22,4	0.902	22,9	0.916	23,2	0.930	23,6	0.936	23,8	0.944	24,0	0.950	24,1	0.956	24,3	1" (25,4)
1.032	26,2	1.060	27,0	1.084	27,6	1.106	28,1	1.120	28,5	1.134	28,8	1.152	29,3	1.166	29,6	1.180	30,0	1.186	30,2	1.194	30,4	1.200	30,5	1.206	30,7	1.1/4" (31,8)
1.282	32,5	1.310	33,3	1.334	33,9	1.356	34,4	1.370	34,8	1.384	35,1	1.402	35,6	1.416	35,9	1.430	36,3	1.436	36,5	1.444	36,7	1.450	36,8	1.456	37,0	1.1/2" (38,1)
1.532	38,8	1.560	39,6	1.584	40,2	1.606	40,7	1.620	41,1	1.634	41,4	1.652	41,9	1.666	42,2	1.680	42,6	1.686	42,8	1.694	43,0	1.700	43,1	1.706	43,3	1.3/4" (44,4)
1.782	45,2	1.810	46,0	1.834	46,6	1.856	47,1	1.870	47,5	1.884	47,8	1.902	48,3	1.916	48,6	1.930	49,0	1.936	49,2	1.944	49,4	1.950	49,5	1.956	49,7	2" (50,8)
2.032	51,5	2.060	52,3	2.084	52,9	2.106	53,4	2.120	53,8	2.134	54,1	2.152	54,6	<u> </u> -	-	<u> </u> -	 -	<u> </u> -	-	<u> </u> -	-	-	 	<u> </u> -	 	2.1/4" (57,1)
2.282	57,9	2.310	58,7	2.334	59,3	2.356	59,8	2.370	60,2	2.384	60,5	2.402	61,0	<u> </u> -	-	-	-	-	-	-	-	-	-	-	 -	2.1/2" (63,5)
2.532	64,2	2.560	65,0	2.584	65,6	2.606	66,1	2.620	66,5	2.634	66,8	2.652	67,3	<u> </u> -	-	-	-	-	-	-	-	-	-	-	-	2.3/4" (69,8)
2.782	70,6	2.810	71,4	2.834	72,0	2.856	72,5	2.870	72,9	2.884	73,2	2.902	73,7	_	-	-	-	-	-	_	-	-	 -	-	-	3" (76,2)
3.032	77,0	3.060	77,8	3.084	78,4	3.106	78,9	3.120	79,3	3.134	79,6	3.152	80,1	-	-	-	-	-	-	-	-	-	<u> </u>	-	- I	3.1/4" (82,6)
3.282	83,3	3.310	84,1	3.334	84,7	3.356	85,2	3.370	85,6	3.384	85,9	3.402	86,4	-	-	-	<u> </u>	-	-	-	-	-	-	-	-	3.1/2" (88,9)
3.532	89,6	3.560	90,4	3.584	91,0	3.606	91,5	3.620	91,9	3.634	92,2	3.652	92,7	-	-	-	! -	-	-	-	-	-		-	! -	3.3/4" (95,2)
3.782	96,0	3.810	96,8	3.834	97,4	3.856	97,9	3.870	98,3	3.884	98,6	3.902	99,1	<u> </u> -	-	-	<u> </u>	-	-	-	-	-		-	: - I	4" (101,6)
4.032	102,4	4.060	103,2	4.084	103,8	4.106	104,3	4.120	104,7	4.134	105,0	4.152	105,5	<u> </u> -	-	-	<u> </u>	-	-	<u> </u> -	-	_		-	: : : -	4.1/4" (108,0)
4 282	108,7	4.310	109,5	4.334	110,1	4.356	110,6	4.370	111,0	4.384	111,3	4.402	111,8	<u> </u> _	_	<u> </u> -	<u> </u>	_	<u> </u>	<u> </u> -	_	_	: : : : :	<u> </u> -	: : :	4.1/2" (114,3)

Pag. 41 ENG / REV 01/23

Heat exchanger's world

MAUS ITALIA SPA IS THE **WORLD LEADING MANUFACTURER** OF TOOLS AND MACHINES FOR THE PRODUCTION AND MAINTENANCE OF HEAT EXCHANGERS



Maus Italia S.p.A.

SP 415 KM 30 (nuova strada di arrocco) 26010 Bagnolo Cremasco (CR) Italy PIVA: 00141010199

Telefono: +39 0373 2370

expo@mausitalia.it www.mausitalia.it

Pag. 42 ENG / REV 01/23





mausitalia.it

